

Product data sheet

Specifications

SQUARE D



Pneumatic Timer - on delay - 0.1-60 seconds - 230/250VDC - SPDT

9050HO10EV66

⚠ Discontinued on: Oct 11, 2019

⚠ Discontinued

Main

| | |
|-------------------|--------------------------|
| Product Range | 9050A/H |
| Product Type | Timer |
| Timing Mode | On-delay |
| Timing Range | 0.15 s...1 min |
| Switch Function | SPDT |
| Coil Voltage | 230/250 V DC |
| Contact Operation | Time delayed 1 NO + 1 NC |
| Current Rating | 15 A |

Complementary

| | |
|---------------------------|---------------------------------------|
| Maximum Switching Voltage | 250 V DC |
| Electrical Connection | Screw-clamp terminals |
| Reset Response Time | 50 ms - on-delay 70 ms - off-delay |
| Mounting Support | Panel |

Environment

| | |
|---|--------------------------|
| Ambient Temperature Range - Operational | 68...104 °F (20...40 °C) |
| Certifications | UL Listed CSA |
| Height | 2.95 in (75 mm) |
| Width | 4.72 in (120 mm) |
| Depth | 4.09 in (104 mm) |

Ordering and shipping details

| | |
|-------------------|------------------------------------|
| Category | 21635-9050 C,H DC PNEUMATIC TIMERS |
| Discount Schedule | CP1 |
| Gtin | 00785901479741 |
| Returnability | No |
| Country Of Origin | MX |

Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months