

# 9050HO20EV51

Pneumatic Timer - on delay - 0.1-60 seconds -  
12VDC - DPDT



Price\*\* : 854.00 USD



9050HO20EV51 has not been replaced. Please contact your customer care center for more information.

## Main

Product range	9050A/H
Product type	Timer
Timing mode	On-delay
Timing range	0.15 s...1 min
Switch function	DPDT
Coil voltage	12 V DC
Contact operation	Time delayed 2 NO + 2 NC
Line Rated Current	10 A

## Complementary

Maximum switching voltage	250 V DC
Electrical connection	Screw-clamp terminals
Reset response time	50 ms - on-delay 70 ms - off-delay
Mounting support	Panel

## Environment

Ambient temperature range - operational	68...104 °F
Certifications	CSA UL listed
Height	2.95 in (75 mm)
Width	4.72 in (120 mm)
Depth	3.74 in (95 mm)

## Ordering and shipping details

Category	21635 - 9050 C,H DC PNEUMATIC TIMERS
----------	--------------------------------------

Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	2.9300000000000002
Returnability	N
Country of origin	MX

**Offer Sustainability**

RoHS (date code: YYWW)	Will be compliant on 3Q2014 <a href="#">Will be compliant on 3Q2014</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------