

# 9050HO20EV66

Pneumatic Timer - on delay - 0.1-60 seconds -  
230/250VDC - DPDT



Price\*\* : 854.00 USD



9050HO20EV66 has not been replaced. Please contact your customer care center for more information.

## Main

|                    |                          |
|--------------------|--------------------------|
| Product range      | 9050A/H                  |
| Product type       | Timer                    |
| Timing mode        | On-delay                 |
| Timing range       | 0.15 s...1 min           |
| Switch function    | DPDT                     |
| Coil voltage       | 230/250 V DC             |
| Contact operation  | Time delayed 2 NO + 2 NC |
| Line Rated Current | 10 A                     |

## Complementary

|                           |                                       |
|---------------------------|---------------------------------------|
| Maximum switching voltage | 250 V DC                              |
| Electrical connection     | Screw-clamp terminals                 |
| Reset response time       | 50 ms - on-delay<br>70 ms - off-delay |
| Mounting support          | Panel                                 |

## Environment

|   |                  |
|---|------------------|
| Ambient temperature range - operational | 68...104 °F      |
| Certifications                          | CSA<br>UL listed |
| Height                                  | 2.95 in (75 mm)  |
| Width                                   | 4.72 in (120 mm) |
| Depth                                   | 3.74 in (95 mm)  |

## Ordering and shipping details

|          |                                      |
|----------|--------------------------------------|
| Category | 21635 - 9050 C,H DC PNEUMATIC TIMERS |
|----------|--------------------------------------|

|                       |                    |
|-----------------------|--------------------|
| Discount Schedule     | CP1                |
| GTIN                  | 00785901851646     |
| Nbr. of units in pkg. | 1                  |
| Package weight(Lbs)   | 2.9300000000000002 |
| Returnability         | N                  |
| Country of origin     | MX                 |

**Offer Sustainability**

|                        |  |
|------------------------|--|
| RoHS (date code: YYWW) | Will be compliant on 3Q2014<br><a href="#">Will be compliant on 3Q2014</a>   |
| REACH                  | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a> |

**Contractual warranty**

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|