

Product data sheet

Characteristics

9050JCK1F480V14

Plug-In Timer - On Delay - Fixed Time - 480 seconds - 24VAC/DC

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 87.00 USD



Main

| | |
|----------------|------------|
| Product range | 9050JCK |
| Product type | Timer |
| Timing mode | On-delay |
| Timing range | 480 s |
| Supply voltage | 24 V AC/DC |

Complementary

| | |
|---------------------------|----------------------|
| Power consumption | 2 VA |
| Line Rated Current | 10 A |
| Switch function | DPDT |
| Contact composition | 2 NO + 2 NC |
| Contact material | Silver nickel |
| Maximum switching voltage | 240 V AC |
| Mounting type | Socket |
| Number of pins | 8 |
| Shape of pins | Tubular |
| For use with | 8501NR51 8501NR52 |

Environment

| | |
|---|--|
| Certifications | CE RoHS UL listed UL recognized |
| Ambient temperature range - operational | -18...150 °F |
| Height | 2.4 in (61 mm) |

| | |
|-------|------------------|
| Width | 1.69 in (43 mm) |
| Depth | 4.09 in (104 mm) |

Ordering and shipping details

| | |
|-----------------------|--|
| Category | 21651 - 9050 JCK(NOT JCK60, 70) G P TIMERS |
| Discount Schedule | CP2 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.33000000000000002 |
| Returnability | N |
| Country of origin | US |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 0627 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product environmental profile | Available |
| Product end of life instructions | Available |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|