# Product data sheet

Specifications



# Timing Relay, Type JCK, plug In, on delay, fixed time, 5 seconds, 10A, 240 VAC, 120 VAC/110 VDC

9050JCK1F5V20

Product availability: Stock - Normally stocked in distribution facility

#### Price\*: 78.00 USD

#### Main

Product Range	9050JCK	
Product Type	Timer	
Timing Mode	On-delay	
Timing Range	5 s	
Supply Voltage	120 V AC	
	110 V DC	

### Complementary

Power Consumption	2 VA
Current Rating	10 A
Switch Function	DPDT
Contact Composition	2 NO + 2 NC
Contact Material	Silver nickel
Maximum Switching Voltage	240 V AC
Mounting Type	Socket
Number Of Pins	8
Shape Of Pins	Tubular
For Use With	8501NR51 8501NR52

### Environment

Certifications	UL Recognized UL Listed CE
Ambient Temperature Range - Operational	-18150 °F (-2866 °C)
Height	2.40 in (61 mm)
Width	1.69 in (43 mm)
Depth	4.09 in (104 mm)

### Ordering and shipping details

Category	US10CP221651
Discount Schedule	0CP2

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Gtin	785901056492	
Returnability	Yes	
Country Of Origin	US	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.00 in (5.08 cm)
Package 1 Width	2.60 in (6.604 cm)
Package 1 Length	4.50 in (11.43 cm)
Package 1 Weight	3.84 oz (108.862 g)

# **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information