





Timing Relay, Type JCK, plug In, off delay, adjustable time, 0.3 to 30 seconds, 10A, 240 VAC, 120 VAC/ 110 VDC

9050JCK22V20

Product availability: Stock - Normally stocked in distribution facility

Price\*: 98.00 USD

#### Main

| Product Range  | 9050JCK   |  |
|----------------|-----------|--|
| Product Type   | Timer     |  |
| Timing Mode    | Off-delay |  |
| Timing Range   | 0.330 s   |  |
| Supply Voltage | 120 V AC  |  |
|                | 110 V DC  |  |

### Complementary

| Power Consumption         | 2 VA                 |  |
|---------------------------|----------------------|--|
| Current Rating            | 10 A                 |  |
| Switch Function           | DPDT                 |  |
| Contact Composition       | 2 NO + 2 NC          |  |
| Contact Material          | Silver nickel        |  |
| Maximum Switching Voltage | 240 V AC             |  |
| Mounting Type             | Socket               |  |
| Number Of Pins            | 11                   |  |
| Shape Of Pins             | s Tubular            |  |
| For Use With              | 8501NR62<br>8501NR61 |  |

### **Environment**

| Certifications                             | UL Listed<br>CE<br>UL Recognized |
|--|----------------------------------|
| Ambient Temperature Range -<br>Operational | -18150 °F (-2866 °C)             |
| Height                                     | 2.40 in (61 mm)                  |
| Width                                      | 1.69 in (43 mm)                  |
| Depth                                      | 4.09 in (104 mm)                 |

### Ordering and shipping details

Category US10CP221651

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Discount Schedule | 0CP2         |
|-------------------|--------------|
| Gtin              | 785901032625 |
| Returnability     | Yes          |
| Country Of Origin | US           |

## **Packing Units**

| Unit Type Of Package 1       | PCE                 |
|------------------------------|---------------------|
| Number Of Units In Package 1 | 1                   |
| Package 1 Height             | 2.00 in (5.08 cm)   |
| Package 1 Width              | 2.60 in (6.604 cm)  |
| Package 1 Length             | 4.30 in (10.922 cm) |
| Package 1 Weight             | 4.00 oz (113.398 g) |

# **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

| <b>Ø</b> | Reach Free Of Svhc         |     |
|----------|----------------------------|-----|
| <b>②</b> | Toxic Heavy Metal Free     |     |
| <b>②</b> | Mercury Free               |     |
| <b>⊘</b> | Rohs Exemption Information | Yes |

### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| China Rohs Regulation    | China RoHS declaration  |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | End of Life Information   |