





Timing Relay, Type JCK, plug In, off delay, adjustable time, 1.8 to 180 seconds, 10A, 240 VAC, 24 VAC/DC

9050JCK25V14

(!) Discontinued on: Jun 30, 2023

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product Range	9050JCK	
Product Type	Timer	
Timing Mode	Off-delay	
Timing Range	1.8180 s	
Supply Voltage	24 V AC/DC	

### Complementary

Power Consumption	2 VA	
Current Rating	10 A	
Switch Function DPDT		
Contact Composition	tact Composition 2 NO + 2 NC	
Contact Material	Silver nickel	
Maximum Switching Voltage	240 V AC	
Mounting Type	Socket	
Number Of Pins	11	
Shape Of Pins	Pins Tubular	
For Use With	8501NR61 8501NR62	

### **Environment**

Certifications	UL Listed CE UL Recognized
Ambient Temperature Range - Operational	-18150 °F (-2866 °C)
Height	2.40 in (61 mm)
Width	1.69 in (43 mm)
Depth	4.09 in (104 mm)

### Ordering and shipping details

Category US10CP221651

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	0CP2
Gtin	785901032779
Returnability	Yes
Country Of Origin	US

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.00 in (5.08 cm)
Package 1 Width	2.60 in (6.604 cm)
Package 1 Length	4.40 in (11.176 cm)
Package 1 Weight	4.32 oz (122.47 g)

# **Contractual warranty**

Warranty 18 months



**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>②</b>	Toxic Heavy Metal Free	
<b>9</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information