




Price\*\* : 98.00 USD



9050JCK2F.25V14 has not been replaced. Please contact your customer care center for more information.

### Main

Product range	9050JCK
Product type	Timer
Timing mode	Off-delay
Timing range	0.25 s
Supply voltage	24 V AC/DC

### Complementary

Power consumption	2 VA
Line Rated Current	10 A
Switch function	DPDT
Contact composition	2 NO + 2 NC
Contact material	Silver nickel
Maximum switching voltage	240 V AC
Mounting type	Socket
Number of pins	11
Shape of pins	Tubular
For use with	8501NR61 8501NR62

### Environment

Certifications	CE RoHS UL listed UL recognized
Ambient temperature range - operational	-18...150 °F
Height	2.4 in (61 mm)
Width	1.69 in (43 mm)

---

Depth	4.09 in (104 mm)
-------	------------------

---

**Ordering and shipping details**

---

Category	21651 - 9050 JCK(NOT JCK60, 70) G P TIMERS
Discount Schedule	CP2
GTIN	00785901667353
Nbr. of units in pkg.	1
Package weight(Lbs)	0.33000000000000002
Returnability	N
Country of origin	US

---

**Offer Sustainability**

---

RoHS (date code: YYWW)	Compliant - since 0627 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
------------------------	---

---

**Contractual warranty**

---

Warranty period	18 months
-----------------	-----------

---