

Product data sheet

Specifications

SQUARE D



Plug In Timer, off delay, 25 seconds fixed, 120 VAC 110 VDC

9050JCK2F25V20

Discontinued on: Dec 19, 2019

Discontinued

Main

Product Range	9050JCK
Product Type	Timer
Timing Mode	Off-delay
Timing Range	25 s
Supply Voltage	120 V AC 110 V DC

Complementary

Power Consumption	2 VA
Current Rating	10 A
Switch Function	DPDT
Contact Composition	2 NO + 2 NC
Contact Material	Silver nickel
Maximum Switching Voltage	240 V AC
Mounting Type	Socket
Number Of Pins	11
Shape Of Pins	Tubular
For Use With	8501NR61 8501NR62

Environment

Certifications	CE UL Listed UL Recognized
Ambient Temperature Range - Operational	-18...150 °F (-28...66 °C)
Height	2.40 in (61 mm)
Width	1.69 in (43 mm)
Depth	4.09 in (104 mm)

Ordering and shipping details

Category	21651-9050 JCK(NOT JCK60, 70) G P TIMERS
Discount Schedule	CP2
Gtin	00785901834519

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
Country Of Origin	US

Contractual warranty

Warranty	18 months
----------	-----------