# Product data sheet

Specifications



# Plug In Timer, interval, 0.1 to 10 seconds, 24 VAC/DC

9050JCK31V14

Discontinued on: Jan 23, 2021

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product Range	9050JCK
Product Type	Timer
Timing Mode	Interval
Timing Range	0.110 s
Supply Voltage	24 V AC/DC

#### Complementary

2 VA 10 A
10 A
DPDT
2 NO + 2 NC
Silver nickel
240 V AC
Socket
8
Tubular
8501NR51 8501NR52

#### Environment

Certifications	UL Recognized UL Listed CE
Ambient Temperature Range - Operational	-18150 °F (-2866 °C)
Height	2.40 in (61 mm)
Width	1.69 in (43 mm)
Depth	4.09 in (104 mm)

## Ordering and shipping details

Category	US10CP221651
Discount Schedule	0CP2
Gtin	00785901032878

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Returnability	No
Country Of Origin	US

### **Contractual warranty**

Warranty

18 months

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information