

Product data sheet

Specifications



Plug In Timer, interval, 10 seconds fixed, 120 VAC 110 VDC

9050JCK3F10V20

Discontinued on: Oct 11, 2019

Discontinued

Main

Product Range	9050JCK
Product Type	Timer
Timing Mode	Interval
Timing Range	10 s
Supply Voltage	120 V AC 110 V DC

Complementary

Power Consumption	2 VA
Current Rating	10 A
Switch Function	DPDT
Contact Composition	2 NO + 2 NC
Contact Material	Silver nickel
Maximum Switching Voltage	240 V AC
Mounting Type	Socket
Number Of Pins	8
Shape Of Pins	Tubular
For Use With	8501NR52 8501NR51

Environment

Certifications	UL Recognized CE UL Listed
Ambient Temperature Range - Operational	-18...150 °F (-28...66 °C)
Height	2.40 in (61 mm)
Width	1.69 in (43 mm)
Depth	4.09 in (104 mm)

Ordering and shipping details

Category	21651-9050 JCK(NOT JCK60, 70) G P TIMERS
Discount Schedule	CP2
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	US
-------------------	----

Contractual warranty

Warranty	18 months
----------	-----------