

Product data sheet

Specifications

SQUARE D



Plug In Timer, interval, 1 second fixed, 24 VAC/VDC

9050JCK3F1V14

Discontinued on: Oct 11, 2019

Discontinued

Main

Product Range	9050JCK
Product Type	Timer
Timing Mode	Interval
Timing Range	1 s
Supply Voltage	24 V AC/DC

Complementary

Power Consumption	2 VA
Current Rating	10 A
Switch Function	DPDT
Contact Composition	2 NO + 2 NC
Contact Material	Silver nickel
Maximum Switching Voltage	240 V AC
Mounting Type	Socket
Number Of Pins	8
Shape Of Pins	Tubular
For Use With	8501NR52 8501NR51

Environment

Certifications	UL Listed UL Recognized CE
Ambient Temperature Range - Operational	-18...150 °F (-28...66 °C)
Height	2.40 in (61 mm)
Width	1.69 in (43 mm)
Depth	4.09 in (104 mm)

Ordering and shipping details

Category	21651-9050 JCK(NOT JCK60, 70) G P TIMERS
Discount Schedule	CP2
Gtin	00785901425724

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
Country Of Origin	US

Contractual warranty

Warranty	18 months
----------	-----------