

Product data sheet

Characteristics

9050JCK3F60V20

Plug-In Timer - Interval - Fixed Time - 60 seconds
- 120VAC/110VDC



Price* : 78.00 USD



9050JCK3F60V20 has not been replaced. Please contact your customer care center for more information.

⚠ Discontinued

Main

Range of product	9050JCK
Product or component type	Timer
Time delay type	Interval
Time delay range	60 s
[Uc] control circuit voltage	110 V DC 120 V AC

Complementary

Hold-in power consumption in VA	2 VA
Line Rated Current	10 A
Switch function	DPDT
Contacts type and composition	2 NO + 2 NC
Contacts material	Silver nickel
Maximum switching voltage	240 V AC
Mounting support	Socket
Pin number	8
Shape of pin	Tubular
Product compatibility	8501NR52 8501NR51

Environment


Product certifications	UL recognized CE RoHS UL listed
Ambient air temperature for operation	-18...150 °F
Height	2.4 in (61 mm)
Width	1.69 in (43 mm)

Depth	4.09 in (104 mm)
-------	------------------

Ordering and shipping details

Category	21651 - 9050 JCK(NOT JCK60, 70) G P TIMERS
Discount Schedule	CP2
GTIN	00785901835400
Nbr. of units in pkg.	1
Package weight(Lbs)	0.33000000000000002
Returnability	N
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0627 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
------------------------	---

Contractual warranty

Warranty period	18 months
-----------------	-----------
