

Product data sheet

Characteristics

9050JCK42V36

Plug-In Timer - One Shot - 0.3-30 seconds - 12VAC/DC



Price* : 98.00 USD



9050JCK42V36 has not been replaced. Please contact your customer care center for more information.

Main

Product range	9050JCK
Product type	Timer
Timing mode	One shot
Timing range	0.3...30 s
Supply voltage	12 V AC/DC

Complementary

Power consumption	2 VA
Line Rated Current	10 A
Switch function	DPDT
Contact composition	2 NO + 2 NC
Contact material	Silver nickel
Maximum switching voltage	240 V AC
Mounting type	Socket
Number of pins	11
Shape of pins	Tubular
For use with	8501NR61 8501NR62

Environment

Certifications	UL listed RoHS UL recognized CE
Ambient temperature range - operational	-18...150 °F
Height	2.4 in (61 mm)
Width	1.69 in (43 mm)

Depth	4.09 in (104 mm)
-------	------------------

Ordering and shipping details

Category	21651 - 9050 JCK(NOT JCK60, 70) G P TIMERS
Discount Schedule	CP2
GTIN	00785901423263
Nbr. of units in pkg.	1
Package weight(Lbs)	0.33000000000000002
Returnability	N
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0627 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference contains SVHC above the threshold - Go to CaP for more details Go to CaP for more details
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------