



Price** : 140.00 USD



9050JCK5F180V20 has not been replaced. Please contact your customer care center for more information.

Main

| | |
|----------------|----------------------|
| Product range | 9050JCK |
| Product type | Timer |
| Timing mode | Repeat cycle |
| Timing range | 180 s |
| Supply voltage | 110 V DC 120 V AC |

Complementary

| | |
|---------------------------|----------------------|
| Power consumption | 2 VA |
| Line Rated Current | 10 A |
| Switch function | DPDT |
| Contact composition | 2 NO + 2 NC |
| Contact material | Silver nickel |
| Maximum switching voltage | 240 V AC |
| Mounting type | Socket |
| Number of pins | 8 |
| Shape of pins | Tubular |
| For use with | 8501NR51 8501NR52 |

Environment

| | |
|---|--|
| Certifications | CE RoHS UL listed UL recognized |
| Ambient temperature range - operational | -18...150 °F |
| Height | 2.4 in (61 mm) |

| | |
|-------|------------------|
| Width | 1.69 in (43 mm) |
| Depth | 4.09 in (104 mm) |

Ordering and shipping details

| | |
|-----------------------|--|
| Category | 21651 - 9050 JCK(NOT JCK60, 70) G P TIMERS |
| Discount Schedule | CP2 |
| GTIN | 00785901701927 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.33000000000000002 |
| Returnability | N |
| Country of origin | US |

Offer Sustainability

| | |
|------------------------|---|
| RoHS (date code: YYWW) | Compliant - since 0627 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
|------------------------|---|

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|