

9070EL1D9

INDUSTRIAL CONTROL TRANSFORMER 50VA MULTI-VOLTAGE WITH 610mm/24INCH LEADS

Product availability : Stock - Normally stocked in distribution facility



Price** : 230.00 USD



Main

Product or component type	Industrial Control Transformer
Range of product	EL

Complementary

Phase	1 phase
Rated power in VA	50 VA
Primary voltage	480 V 460 V 440 V
Secondary voltage	110 V 115 V 120 V
Temperature rise	55 °C
Electrical connection	Screw clamp terminals
Connector type	610 m lead

Environment

Product certifications	CSA CE UL listed
NEMA degree of protection	Not rated (open device)
Insulation temperature	221 °F (105 °C)

Ordering and shipping details

Category	21691 - 9070 AP,E,G,H,SB
Discount Schedule	CP8
GTIN	00785901020219

Nbr. of units in pkg.	1
Package weight(Lbs)	2.6099999999999999
Returnability	Y
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 4Q2016 Will be compliant on 4Q2016
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------