

# Product data sheet

## Characteristics

# 9070EL2D9

## INDUSTRIAL CONTROL TRANSFORMER

### 100VA MULTI-VOLTAGE WITH 610mm/24INCH LEADS

Product availability : Stock - Normally stocked in distribution facility



Price\*\* : 309.00 USD



### Main

Product or component type	Industrial Control Transformer
Range of product	EL

### Complementary

Phase	1 phase
Rated power in VA	100 VA
Primary voltage	440 V 480 V 460 V
Secondary voltage	115 V 120 V 110 V
Temperature rise	55 °C
Electrical connection	Screw clamp terminals
Connector type	610 m lead

### Environment

Product certifications	CSA CE UL listed
NEMA degree of protection	Not rated (open device)
Insulation temperature	221 °F (105 °C)

### Ordering and shipping details

Category	21691 - 9070 AP,E,G,H,SB
Discount Schedule	CP8

GTIN	00785901020226
Nbr. of units in pkg.	1
Package weight(Lbs)	4.0499999999999998
Returnability	Y
Country of origin	MX

**Offer Sustainability**

RoHS (date code: YYWW)	Will be compliant on 4Q2016 <a href="#">Will be compliant on 4Q2016</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------