

Product data sheet

Characteristics

9070EO18D1

INDUSTRIAL CONTROL TRANSFORMER 75VA 220x440V PRIMARY

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 171.00 USD



Main

Product or component type	Industrial Control Transformer
Range of product	EO

Complementary

Phase	1 phase
Rated power in VA	75 VA
Primary voltage	240 x 480 V 230 x 460 V 220 x 440 V
Secondary voltage	110 V
Temperature rise	80 °C
Electrical connection	Screw clamp terminals

Environment

Product certifications	CE CSA UL listed
NEMA degree of protection	Not rated (open device)
Insulation temperature	266 °F (130 °C)

Ordering and shipping details

Category	21691 - 9070 AP,E,G,H,SB
Discount Schedule	CP8
GTIN	00785901113843
Nbr. of units in pkg.	1
Package weight(Lbs)	3.5

Returnability	Y
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 4Q2016 Will be compliant on 4Q2016
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------