

Product data sheet

Characteristics

9070SK1000G1D1G13

XFMR DISCONNECT 1500VA 240/480V-120V

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 2,520.00 USD



Main

Product	Transformer Disconnect
Certifications	CSA UL listed
Enclosure Type	NEMA 1 standard
Insulation Temperature	356 °F (180 °C)
Phase	1 phase
Primary Voltage	240 x 480 V
Power Rating	1000 VA
Secondary Voltage	120 V
Temperature Rise	115 °C
Electrical Connection	Screw clamp terminals
Type	SK

Ordering and shipping details

Category	21694 - 9070 SK
Discount Schedule	CP8
GTIN	00785901747109
Nbr. of units in pkg.	1
Package weight(Lbs)	38
Returnability	N
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 4Q2016 Will be compliant on 4Q2016
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.

----- More information

For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period

18 months
