

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 4,434.00 USD



Main

Product	Transformer Disconnect
Certifications	CSA UL listed
Enclosure Type	NEMA 12 standard
Insulation Temperature	356 °F (180 °C)
Phase	1 phase
Primary Voltage	240 x 480 V
Power Rating	1500 VA
Secondary Voltage	120 V
Temperature Rise	115 °C
Electrical Connection	Screw clamp terminals
Type	SK

Ordering and shipping details

Category	21694 - 9070 SK
Discount Schedule	CP8
Nbr. of units in pkg.	1
Package weight(Lbs)	62
Returnability	N
Country of origin	US

Contractual warranty

Warranty period	18 months
-----------------	-----------