

# Product data sheet

## Characteristics

# 9070SK1500G2D1

## XFMR DISCONNECT 2000VA 240/480V-120V

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 3,255.00 USD



### Main

Product	Transformer Disconnect
Certifications	CSA UL listed
Enclosure Type	NEMA 1 standard
Insulation Temperature	356 °F (180 °C)
Phase	1 phase
Primary Voltage	240 x 480 V
Power Rating	1500 VA
Secondary Voltage	120 V
Temperature Rise	115 °C
Electrical Connection	Screw clamp terminals
Type	SK

### Ordering and shipping details

Category	21694 - 9070 SK
Discount Schedule	CP8
GTIN	00785901099505
Nbr. of units in pkg.	1
Package weight(Lbs)	67
Returnability	N
Country of origin	US

### Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 4Q2016 <a href="#">Will be compliant on 4Q2016</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.

---

----- More information

For more information go to [www.p65warnings.ca.gov](http://www.p65warnings.ca.gov)

---

### Contractual warranty

---

Warranty period

18 months

---