

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 3,819.00 USD



Main

Device short name	SK
Enclosure type	Standard environment enclosure indoor
Product or component type	Power supply source
Provided equipment	Vario V3 switch-disconnector
Range of product	Square D

Complementary

Depth	12.21 in
Design	Standard
Device mounting	Surface
Electrical connection	Screw clamp terminal
Height	13.4 in
Material	Copper winding
Mounting support	Panel
Network number of phases	1 phase
Primary voltage	240 x 480 V
Rated power in VA	2000 VA
Rated voltage	120 V auxiliary power supply 120 V isolated
Secondary voltage	120 V
Temperature rise	115 °C
Width	14.8 in

Environment

Insulation temperature	356 °F (180 °C)
NEMA degree of protection	NEMA 1
Product certifications	UL listed file E61239

Ordering and shipping details

Category	21694 - 9070 SK
Discount Schedule	CP8
GTIN	00785901712022
Nbr. of units in pkg.	1
Package weight(Lbs)	73
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 4Q2016 Will be compliant on 4Q2016
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------