

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 4,412.00 USD



### Main

Device application	Power supply
Device short name	SK
Enclosure type	Standard environment enclosure indoor
Provided equipment	Vario V3 switch-disconnector
Range of product	Square D

### Complementary

Depth	310.13 mm (12.21 in)
Design	Standard
Device mounting	Surface
Electrical connection	Screw clamp terminal
Height	340.36 mm (13.4 in)
Material	Copper winding
Mounting support	panel
Phase	1 phase
Primary voltage	240 x 480 V
Rated power in VA	2000 VA
Rated voltage	120 V auxiliary power supply 120 V isolated
Secondary voltage	120 V
Temperature rise	115 °C
Width	375.92 mm (14.8 in)

### Environment

Insulation temperature	356 °F (180 °C)
NEMA degree of protection	NEMA 1
Product certifications	UL listed file E61239

### Ordering and shipping details

Category	21694 - 9070 SK
Discount Schedule	CP8
GTIN	00785901284451
Package weight(Lbs)	33.11 kg (73 lb(US))
Returnability	No

### Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl Glycidyl Ether which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.

### Contractual warranty

Warranty	18 months
----------	-----------