

# 9070T1000D32

## TRFMR CONTROL 1000VA MULTIPLEVOLTAGES

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 837.00 USD



### Main

Product or component type	Industrial Control Transformer
Power Rating	1000 VA
Primary Voltage	230/460/575 V
Secondary Voltage	95/115 V
Type	T

### Complementary

Phase	1 phase
Power Rating	1000 VA per UL 1000 VA per CSA 1000 VA per NOM 630 VA per CE
Primary to Secondary Voltage	230/460/575 V : 95/115 V
Temperature rise	115 °C
Electrical connection	Screw clamp terminals
Height	6.17 in
Width	7.06 in
Depth	5.92 in
Material	Copper winding
Fingersafe Cover Compatibility	FSC2

### Environment

Product certifications	CE UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation temperature	356 °F (180 °C)

## Ordering and shipping details

Category	16201 - 9070 T (NOT TF) 250-2000VA
Discount Schedule	CP8
GTIN	00785901313700
Nbr. of units in pkg.	1
Package weight(Lbs)	31.300000000000001
Returnability	N
Country of origin	US

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1227 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	10 years
-----------------	----------