

# Product data sheet

## Characteristics

# 9070T1000D37

## TRANSFORMER CONTROL 1000VA

### 600V-120/240V

Product availability : Stock - Normally stocked in distribution facility



Price\*\* : 891.00 USD



### Main

Product or component type	Industrial Control Transformer
Power Rating	1000 VA
Primary Voltage	600 V 575 V
Secondary Voltage	120/240 V 115/230 V
Type	T

### Complementary

Phase	1 phase
Power Rating	1000 VA per UL 1000 VA per CSA 1000 VA per NOM 630 VA per CE
Primary to Secondary Voltage	575 V : 115/230 V 600 V : 120/240 V
Temperature rise	115 °C
Electrical connection	Screw clamp terminals
Height	4.51 in
Width	5.25 in
Depth	6.3 in
Fingersafe Cover Compatibility	FSC2

### Environment

Product certifications	CE CSA UL listed
Enclosure Type	Not rated (open device)

Insulation temperature	356 °F (180 °C)
------------------------	-----------------

### Ordering and shipping details

Category	16201 - 9070 T (NOT TF) 250-2000VA
Discount Schedule	CP8
GTIN	00785901803539
Nbr. of units in pkg.	1
Package weight(Lbs)	20.800000000000001
Returnability	Y
Country of origin	US

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1227 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	10 years
-----------------	----------