





Transformer, Type T, industrial control, 100VA, 1 phase, 380V primary, 240V secondary, 55C rise

9070T100D12

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 219.00 USD

Main

| Product Type | Industrial Control Transformer |
|--------------|--------------------------------|
| Туре | Т |

Complementary

| Number Of Phases | 1 phase | |
|--------------------------------|-----------------------|--|
| Power Rating | 100 VA UL | |
| | 100 VA CSA | |
| | 100 VA NOM | |
| | 100 VA CE | |
| Primary To Secondary Voltage | 480 V 240 V | |
| | 460 V 230 V | |
| | 440 V 220 V | |
| Temperature Rise | 55 °C | |
| Electrical Connection | Screw clamp terminals | |
| Height | 2.89 in (73.41 mm) | |
| Width | 3.38 in (85.85 mm) | |
| Depth | 3.34 in (84.84 mm) | |
| Material | Copper: winding | |
| Fingersafe Cover Compatibility | FSC1 | |

Environment

| Certifications | CSA file LR37055 guide 184-N-90 UL listed file E61239 |
|------------------------|--|
| Enclosure Type | Not rated (open device) |
| Insulation Temperature | 221 °F (105 °C) |

Ordering and shipping details

| Category | US10CP816206 | |
|-------------------|--------------|--|
| Discount Schedule | 0CP8 | |
| Gtin | 785901845478 | |
| Returnability | No | |
| Country Of Origin | US | |

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Unit Type Of Package 1 | PCE |
|------------------------------|------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 3.80 in (9.652 cm) |
| Package 1 Width | 3.90 in (9.906 cm) |
| Package 1 Length | 4.00 in (10.16 cm) |
| Package 1 Weight | 3.80 lb(US) (1.724 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |