

9070T100D17

INDUSTRIAL CONTROL TRANSFORMER

100VA 415V

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 477.00 USD



Main

Product or component type	Industrial Control Transformer
Power Rating	100 VA
Primary Voltage	415 V
Secondary Voltage	110 V
Type	T

Complementary

Phase	1 phase
Power Rating	100 VA
Primary to Secondary Voltage	415 V : 110 V
Temperature rise	55 °C
Electrical connection	Screw clamp terminals
Fingersafe Cover Compatibility	FSC1

Environment

Product certifications	CE CSA UL listed
Enclosure Type	Not rated (open device)
Insulation temperature	221 °F (105 °C)

Ordering and shipping details

Category	16200 - 9070 T (NOT TF) 50-200VA
Discount Schedule	CP8
GTIN	00785901763536
Nbr. of units in pkg.	1

Package weight(Lbs)	3.8000000000000003
Returnability	N
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1227 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------