

Product availability : Stock - Normally stocked in distribution facility



Price\*\* : 207.00 USD



### Main

Product or component type	Industrial Control Transformer
Power Rating	100 VA
Primary Voltage	230/460/575 V
Secondary Voltage	95/115 V
Type	T

### Complementary

Phase	1 phase
Power Rating	100 VA
Primary to Secondary Voltage	230/460/575 V : 95/115 V
Temperature rise	55 °C
Electrical connection	Screw clamp terminals
Height	3.2 in
Width	3.75 in
Depth	3.59 in
Material	Copper winding
Fingersafe Cover Compatibility	FSC1

### Environment

Product certifications	CE UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation temperature	221 °F (105 °C)

### Ordering and shipping details

Category	16200 - 9070 T (NOT TF) 50-200VA
----------	----------------------------------

Discount Schedule	CP8
GTIN	00785901322269
Nbr. of units in pkg.	1
Package weight(Lbs)	5.54
Returnability	Y
Country of origin	MX

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1227 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	10 years
-----------------	----------