

Product availability : Stock - Normally stocked in distribution facility



Price\*\* : 489.00 USD



### Main

Product or component type	Industrial Control Transformer
Power Rating	100 VA
Primary Voltage	600 V 575 V
Secondary Voltage	120/240 V 115/230 V
Type	T

### Complementary

Phase	1 phase
Power Rating	100 VA
Primary to Secondary Voltage	575 V : 115/230 V 600 V : 120/240 V
Temperature rise	55 °C
Electrical connection	Screw clamp terminals
Height	2.89 in
Width	3.38 in
Depth	3.34 in
Fingersafe Cover Compatibility	FSC1

### Environment

Product certifications	CE CSA UL listed
Enclosure Type	Not rated (open device)
Insulation temperature	221 °F (105 °C)

**Ordering and shipping details**

Category	16200 - 9070 T (NOT TF) 50-200VA
Discount Schedule	CP8
GTIN	00785901689003
Nbr. of units in pkg.	1
Package weight(Lbs)	3.8999999999999999
Returnability	Y
Country of origin	US

**Offer Sustainability**

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1227 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	10 years
-----------------	----------