

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 1,224.00 USD



Main

Product or component type	Industrial Control Transformer
Power Rating	1500 VA
Primary Voltage	240 x 480 V
Secondary Voltage	24/120 V
Type	T

Complementary

Phase	1 phase
Power Rating	1500 VA per UL 1500 VA per CSA 1500 VA per NOM 1000 VA per CE
Primary to Secondary Voltage	240 x 480 V : 24/120 V
Temperature rise	115 °C
Electrical connection	Screw clamp terminals
Height	6.17 in
Width	7.06 in
Depth	5.92 in
Material	Copper winding
Fingersafe Cover Compatibility	FSC2

Environment

Product certifications	CE UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation temperature	356 °F (180 °C)

Ordering and shipping details

Category	16201 - 9070 T (NOT TF) 250-2000VA
Discount Schedule	CP8
GTIN	00785901551300
Nbr. of units in pkg.	1
Package weight(Lbs)	34.5
Returnability	N
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1227 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	10 years
-----------------	----------