

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 1,076.00 USD



### Main

Product or component type	Industrial Control Transformer
Power Rating	1500 VA
Primary Voltage	115 V 120 V 110 V
Secondary Voltage	120 V 115 V 110 V
Type	T

### Complementary

Phase	1 phase
Power Rating	1500 VA per UL 1500 VA per CSA 1500 VA per NOM 1000 VA per CE
Primary to Secondary Voltage	110 V : 110 V 115 V : 115 V 120 V : 120 V
Temperature rise	115 °C
Electrical connection	Screw clamp terminals
Height	6.16 in
Width	7.06 in
Depth	5.81 in
Material	Copper winding
Fingersafe Cover Compatibility	FSC2

### Environment

Product certifications	CE UL listed file E61239
------------------------	-----------------------------

Enclosure Type	Not rated (open device)
Insulation temperature	356 °F (180 °C)

### Ordering and shipping details

Category	16201 - 9070 T (NOT TF) 250-2000VA
Discount Schedule	CP8
Nbr. of units in pkg.	1
Package weight(Lbs)	34.100000000000001
Returnability	N
Country of origin	US

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1227 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	10 years
-----------------	----------