Product data sheet

Specifications







Transformer, Type T, industrial control, 200VA, 1 phase, 208V primary, 120V secondary, 80C rise

9070T200D3

Product availability: Stock - Normally stocked in distribution facility

Price*: 352.00 USD

Main

| Product Type | Industrial Control Transformer |
|--------------|--------------------------------|
| Туре | Т |

Complementary

| Number Of Phases | 1 phase | |
|--------------------------------|-----------------------|--|
| Power Rating | 200 VA UL | |
| | 200 VA CSA | |
| | 200 VA NOM | |
| | 200 VA CE | |
| Primary To Secondary Voltage | 208 V 120 V | |
| Temperature Rise | 80 °C | |
| Electrical Connection | Screw clamp terminals | |
| Height | 3.2 in (81.28 mm) | |
| Width | 3.75 in (95.25 mm) | |
| Depth | 3.59 in (91.19 mm) | |
| Material | Copper: winding | |
| Fingersafe Cover Compatibility | FSC1 | |

Environment

| Certifications | CSA file LR37055 guide 184-N-90 UL listed file E61239 |
|------------------------|--|
| Enclosure Type | Not rated (open device) |
| Insulation Temperature | 266 °F (130 °C) |

Ordering and shipping details

| Category | US10CP816200 |
|-------------------|--------------|
| Discount Schedule | 0CP8 |
| Gtin | 785901845454 |
| Returnability | Yes |
| Country Of Origin | US |

Packing Units

Unit Type Of Package 1

PCE

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Number Of Units In Package 1 | 1 |
|------------------------------|------------------------|
| Package 1 Height | 5.63 in (14.3 cm) |
| Package 1 Width | 6.22 in (15.8 cm) |
| Package 1 Length | 7.01 in (17.8 cm) |
| Package 1 Weight | 5.91 lb(US) (2.681 kg) |

Contractual warranty

Warranty

10 Years

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |