

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 716.00 USD



Main

Product or component type	Industrial Control Transformer
Power Rating	250 VA
Primary Voltage	277 V
Secondary Voltage	24 V
Type	T

Complementary

Phase	1 phase
Power Rating	250 VA per UL 250 VA per CSA 250 VA per NOM 160 VA per CE
Primary to Secondary Voltage	277 V : 24 V
Temperature rise	80 °C
Electrical connection	Screw clamp terminals
Height	3.25 in
Width	3.75 in
Depth	5.25 in
Material	Copper winding
Fingersafe Cover Compatibility	FSC2

Environment

Product certifications	CE UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation temperature	266 °F (130 °C)

Ordering and shipping details

Category	16201 - 9070 T (NOT TF) 250-2000VA
Discount Schedule	CP8
Nbr. of units in pkg.	1
Package weight(Lbs)	7.299999999999998
Returnability	N
Country of origin	US

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1227 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	10 years
-----------------	----------