

# Product data sheet

Specifications

SQUARE D



Transformer, Type T, industrial control, 3000VA, 1 phase, 200V primary, 115V secondary, 115C rise

9070T3000D93

! Discontinued on: Jan 2, 2024

! Discontinued

## Main

Product Type	Industrial Control Transformer
Type	T

## Complementary

Number Of Phases	1 phase
Power Rating	3000 VA UL 3000 VA CSA 3000 VA NOM 2000 VA CE
Primary To Secondary Voltage	200 V 115 V
Temperature Rise	115 °C
Electrical Connection	Screw clamp terminals
Fingersafe Cover Compatibility	FSC2

## Environment

Certifications	CSA UL Listed
Enclosure Type	Not rated (open device)
Insulation Temperature	356 °F (180 °C)

## Ordering and shipping details

Category	16205-9070 T (NOT TF) 3000 - 5000VA
Discount Schedule	CP8
Gtin	3606486985397
Returnability	No

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	60.00 lb(US) (27.216 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

