Product data sheet

Specifications







Industrial control transformer, Type TF, 1 phase, 100VA, 240x480V primary, 120/240V secondary, 50/60Hz

9070TF100D31

Product availability: Stock - Normally stocked in distribution facility

Price*: 676.00 USD

Main

| Product Or Component Type | Industrial Control Transformer |
|---------------------------|--------------------------------|
| Туре | TF |

Complementary

| e emprementar y | |
|--------------------------------|---|
| Number Of Phases | 1 phase |
| Power Rating | 100 VA UL 100 VA CSA 100 VA NOM 100 VA CE |
| Primary To Secondary Voltage | 240 x 480 V 120/240 V 230 x 460 V 115/230 V 220 x 440 V 110/220 V |
| Fuse Type | 0.41 x 1.50 in CC top |
| Temperature Rise | 55 °C |
| Electrical Connection | Screw clamp terminals |
| Height | 4.18 in (106.17 mm) |
| Width | 3.38 in (85.85 mm) |
| Depth | 3.34 in (84.84 mm) |
| Material | Copper: winding |
| Fingersafe Cover Compatibility | FSC1 |

Environment

| Product Certifications | UL listed file E61239 CSA file LR37055 guide 184-N-90 |
|------------------------|--|
| Enclosure Type | Not rated (open device) |
| Insulation Temperature | 221 °F (105 °C) |

Ordering and shipping details

| Category | US10CP816202 |
|-------------------|--------------|
| Discount Schedule | 0CP8 |
| Gtin | 785901712046 |
| Returnability | Yes |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Country Of | Origin | |
|------------|--------|--|
|------------|--------|--|

Packing Units

| <u> </u> | |
|------------------------------|-----------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 6.90 in (17.53 cm) |
| Package 1 Width | 6.30 in (16 cm) |
| Package 1 Length | 7.90 in (20.07 cm) |
| Package 1 Weight | 4.48 lb(US) (2.03 kg) |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |