





Industrial control transformer, Type TF, 1 phase, 150VA, 240/416/480/600V primary, 99/120/130V secondary, 50/60Hz

9070TF150D50



(!) Discontinued on: Jan 2, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

| Product Or Component Type | Industrial Control Transformer |
|---------------------------|--------------------------------|
| Туре                      | TF                             |

## Complementary

| · · ·   - · · · · · · · · · · · · · |                                |  |
|-------------------------------------|--------------------------------|--|
| Number Of Phases                    | 1 phase                        |  |
| Power Rating                        | 150 VA UL                      |  |
|                                     | 150 VA CSA                     |  |
|                                     | 150 VA NOM                     |  |
|                                     | 150 VA CE                      |  |
| Primary To Secondary Voltage        | 240/416/480/600 V 99/120/130 V |  |
|                                     | 230/400/460/575 V 95/115/125 V |  |
|                                     | 220/380/440/550 V 90/110/120 V |  |
|                                     | 208/360/416/520 V 85/100/110 V |  |
| Fuse Type                           | 0.41 x 1.50 in CC top          |  |
| Temperature Rise                    | 55 °C                          |  |
| Electrical Connection               | Screw clamp terminals          |  |
| Height                              | 5.15 in (130.81 mm)            |  |
| Width                               | 4.5 in (114.30 mm)             |  |
| Depth                               | 4.74 in (120.40 mm)            |  |
| Material                            | Copper: winding                |  |
| Fingersafe Cover Compatibility      | FSC23                          |  |

#### **Environment**

| Product Certifications | UL listed file E61239<br>CSA file LR37055 guide 184-N-90 |
|------------------------|--|
| Enclosure Type         | Not rated (open device)                                  |
| Insulation Temperature | 221 °F (105 °C)  |

## Ordering and shipping details

| Category          | US10CP816207 |
|-------------------|--------------|
| Discount Schedule | 0CP8         |
| Gtin              | 785901575351 |
| Returnability     | No           |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin US

# **Packing Units**

| Unit Type Of Package 1       | PCE                    |
|------------------------------|------------------------|
| Number Of Units In Package 1 | 1                      |
| Package 1 Height             | 6.00 in (15.24 cm)     |
| Package 1 Width              | 7.50 in (19.05 cm)     |
| Package 1 Length             | 6.50 in (16.51 cm)     |
| Package 1 Weight             | 8.90 lb(US) (4.037 kg) |

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

|          | Mercury Free               |     |
|----------|----------------------------|-----|
| <b>⊘</b> | Rohs Exemption Information | Yes |
| <b>②</b> | Pvc Free                   |     |

### **Certifications & Standards**

| Reach Regulation          | REACh Declaration   |
|---------------------------|---|
| Eu Rohs Directive         | Compliant with Exemptions   |
| China Rohs Regulation     | China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information.  |
| Environmental Disclosure  | Product Environmental Profile   |
| Circularity Profile       | No need of specific recycling operations  |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |