

# Product data sheet

## Characteristics

# 9070TF2000D50

## TRFMR CONTROL 2000VA

### 208/500V-85/100/110

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 1,733.00 USD



### Main

Product or component type	Industrial Control Transformer
Type	TF

### Complementary

Phase	1 phase
Power Rating	2000 VA per UL 2000 VA per CSA 2000 VA per NOM 1500 VA per CE
Primary to Secondary Voltage	208/360/416/520 V : 85/104/115 V 220/380/440/550 V : 90/110/120 V 230/400/460/575 V : 95/115/125 V 240/416/480/600 V : 99/120/130 V
Fuse type	CC 0.41 x 1.50 in top
Temperature rise	115 °C
Electrical connection	Screw clamp terminals
Height	7.46 in
Width	7.06 in
Depth	5.92 in
Fingersafe Cover Compatibility	FSC23

### Environment

Product certifications	CE UL listed file E61239 CSA file LR37055 guide 184-N-90
Enclosure Type	Not rated (open device)
Insulation temperature	221 °F (105 °C)

## Ordering and shipping details

Category	16203 - 9070 TF (NOT T) 250-1000VA
Discount Schedule	CP8
GTIN	00785901804482
Nbr. of units in pkg.	1
Package weight(Lbs)	57.600000000000001
Returnability	N
Country of origin	US

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1227 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------