





Industrial control transformer, Type TF, 1 phase, 300VA, 240/416/480/600V primary, 99/120/130V secondary, 50/60Hz

9070TF300D50

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 811.00 USD

Main

| Product Or Component Type | Industrial Control Transformer |
|---------------------------|--------------------------------|
| Туре | TF |

Complementary

| o o impromontary | |
|--------------------------------|--------------------------------|
| Number Of Phases | 1 phase |
| Power Rating | 300 VA UL |
| | 300 VA CSA |
| | 300 VA NOM |
| | 200 VA CE |
| Primary To Secondary Voltage | 240/416/480/600 V 99/120/130 V |
| | 230/400/460/575 V 95/115/125 V |
| | 220/380/440/550 V 90/110/120 V |
| | 208/360/416/520 V 85/100/110 V |
| Fuse Type | 0.41 x 1.50 in CC top |
| Temperature Rise | 80 °C |
| Electrical Connection | Screw clamp terminals |
| Height | 5.14 in (130.56 mm) |
| Width | 4.5 in (114.30 mm) |
| Depth | 5.49 in (139.45 mm) |
| Material | Copper: winding |
| Fingersafe Cover Compatibility | FSC23 |

Environment

| Product Certifications | CSA file LR37055 guide 184-N-90 UL listed file E61239 |
|------------------------|--|
| Enclosure Type | Not rated (open device) |
| Insulation Temperature | 266 °F (130 °C) |

Ordering and shipping details

| Category | US10CP816207 |
|-------------------|---------------|
| Discount Schedule | 0CP8 |
| Gtin | 3606486995853 |
| Returnability | No |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin US

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 6.00 in (15.24 cm) |
| Package 1 Width | 7.50 in (19.05 cm) |
| Package 1 Length | 6.50 in (16.51 cm) |
| Package 1 Weight | 11.90 lb(US) (5.398 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |