

# Product data sheet

Specifications

SQUARE D



Terminal block, Linergy, 30 flat terminal connector assembly, natural colored blocks, 40A, 600 V

9080GA630BC

 **Discontinued on:** Oct 8, 2021

 **Discontinued**

**Product availability:** Stock - Normally stocked in distribution facility

## Main

Range Of Product	9080G
Product Type	Terminal block
Color	Natural

## Complementary

Voltage Rating	600 V AC/DC
Current Rating	40 A UL 40 A CSA
Assemblies Consist Of	1 end barrier 2 end clamp(s) 1 mounting track 30 terminal blocks
Wire Size	AWG 22...AWG 12 copper
Mounting Type	9080GH track
Certifications	CSA file 62144 class 6228 01 UL recognized E60616 CCN XCFR2 CE
Protection Type	Fingersafe DIN 57470
Ambient Air Temperature For Operation	-40...257 °F (-40...125 °C)
Electrical Connrection Tightening Torque	Screw terminal zinc plated steel 18...20 lbf.in (2.03...2.26 N.m) : AWG 22...AWG 12 copper)
Height	1.48 in (37.59 mm)
Width	1.8 in (45.72 mm)
Depth	13 in (330.20 mm)

## Ordering and shipping details

Category	21702-9080 G (NOT GCB)
Discount Schedule	CP5
Returnability	No
Country Of Origin	MX

## Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Pvc Free	
Eu Rohs Directive		Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
California Proposition 65		WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>