

Product data sheet

Specifications

SQUARE D



Terminal Block Assembly, Box Lug Connector, Natural Color, 600VAC/DC 110AMP

9080GC68

Price*: 57.00 USD

! Discontinued

Main

Range Of Product	9080G
Product Type	Terminal block
Color	Natural

Complementary

Voltage Rating	600 V AC/DC
Current Rating	110 A UL 85 A CSA
Assemblies Consist Of	1 end barrier 2 end clamp(s) 1 mounting track 8 terminal blocks
Wire Size	AWG 18...AWG 4 copper
Mounting Type	9080GH track
Certifications	CSA file 62144 class 6228 01 CE UL recognized E60616 CCN XCFR2
Ambient Air Temperature For Operation	-40...257 °F (-40...125 °C)
Electrical Connrection Tightening Torque	Lug zinc plated steel 32...35 lbf.in (3.62...3.95 N.m) : AWG 18...AWG 4 copper)
Height	2.13 in (54.10 mm)
Width	1.99 in (50.55 mm)
Depth	6 in (152.40 mm)

Ordering and shipping details

Discount Schedule	CP5
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	16.00 oz (453.592 g)

Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)
