

# Product data sheet

Specifications

SQUARE D



## Terminal Block Assembly, Box Lug Connector, Natural Color, 600VAC/DC 70AMP

9080GK610DMPO

Price\*: 32.10 USD

! Discontinued

### Main

Range Of Product	9080G
Product Type	Terminal block
Color	Natural

### Complementary

Voltage Rating	600 V AC/DC
Current Rating	40 A CSA 70 A UL
Assemblies Consist Of	10 terminal blocks 1 end barrier 1 marker
Wire Size	AWG 22...AWG 10 copper
Mounting Type	Panel
Certifications	CSA file 62144 class 6228 01 CE UL recognized E60616 CCN XCFR2
Ambient Air Temperature For Operation	-40...257 °F (-40...125 °C)
Electrical Connrection Tightening Torque	Lug copper 11...12 lbf.in (1.24...1.36 N.m) : AWG 22...AWG 10 copper)
Height	1.39 in (35.31 mm)
Width	1.4 in (35.56 mm)
Depth	4.4 in (111.76 mm)

### Ordering and shipping details

Discount Schedule	CP5
Returnability	No
Country Of Origin	US

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	16.00 oz (453.592 g)

### Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

---