


# 9080GK625DMPO

Terminal Block Assembly, Box Lug Connector,  
Natural Color, 600VAC/DC 70AMP



Price\* : 75.00 USD



9080GK625DMPO has not been replaced. Please contact your customer care center for more information.

## Main

Range of product	9080G
Product or component type	Terminal block
Color	Natural

## Complementary

System Voltage	600 V AC/DC
Current Rating	40 A per: CSA 70 A per: UL
Assemblies Consist of	End barrier qty: 1 Marker qty: 1 Terminal blocks qty: 25
Wire Size	AWG 22...AWG 10 (copper)
Mounting Type	Panel
Certifications	CE UL recognized E60616 CCN XCFR2 CSA file 62144 class 6228 01
Ambient air temperature for operation	-40...257 °F
Electrical Connrection Tightening Torque	Lug copper Tightening Torque: 11...12 lbf.in for: AWG 22...AWG 10 (copper)
Height	1.39 in
Width	1.4 in
Depth	9.6 in

## Ordering and shipping details

Category	21702 - 9080 G (NOT GCB)
Discount Schedule	CP5
Nbr. of units in pkg.	1
Package weight(Lbs)	1

Returnability	N
Country of origin	MX

**Offer Sustainability**

RoHS (date code: YYWW)	Compliant - since 0847 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------