

# Product data sheet

Specifications

SQUARE D



## Terminal Block Assembly, Box Lug Connector, Natural Color, 600VAC/DC 70AMP

9080GM620T12

! Discontinued

### Main

Range Of Product	9080G
Product Type	Terminal block
Color	Natural

### Complementary

Voltage Rating	600 V AC/DC
Current Rating	30 A UL 30 A CSA
Assemblies Consist Of	1 end barrier 2 end clamp(s) 1 mounting track 20 terminal blocks
Wire Size	AWG 22...AWG 10 copper
Mounting Type	DIN rail
Certifications	CE CSA file 62144 class 6228 01 UL recognized E60616 CCN XCFR2
Protection Type	Fingersafe DIN 57470
Ambient Air Temperature For Operation	-40...257 °F (-40...125 °C)
Electrical Connrection Tightening Torque	Lug zinc plated steel 7...8 lbf.in (0.79...0.90 N.m) : AWG 22...AWG 10 copper)
Height	1.82 in (46.23 mm)
Width	1.72 in (43.69 mm)
Depth	12 in (304.80 mm)

### Ordering and shipping details

Category	21702-9080 G (NOT GCB)
Discount Schedule	CP5
Returnability	No
Country Of Origin	MX

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	16.00 oz (453.592 g)
------------------	----------------------

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

### Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

---