

# 9080GP620

Terminal Block Assembly, Pressure Wire Clamp,  
Natural Color, 600VAC/DC 40AMP



Price\* : 75.00 USD



9080GP620 has not been replaced. Please contact your customer care center for more information.

## Main

Range of product	9080G
Product or component type	Terminal block
Color	Natural

## Complementary

System Voltage	600 V AC/DC
Current Rating	40 A per: UL 40 A per: CSA
Assemblies Consist of	End barrier qty: 1 End clamp(s) qty: 2 Mounting track qty: 1 Terminal blocks qty: 20
Wire Size	AWG 18...AWG 12 (copper)
Mounting Type	9080GH track
Certifications	CE UL recognized E60616 CCN XCFR2 CSA file 62144 class 6228 01
Ambient air temperature for operation	-40...257 °F
Electrical Connection Tightening Torque	Clamp terminal zinc plated steel Tightening Torque: 18...20 lbf.in for: AWG 18...AWG 10 (copper)
Height	1.48 in
Width	1.8 in
Depth	10 in

## Ordering and shipping details

Category	21702 - 9080 G (NOT GCB)
Discount Schedule	CP5
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5

Returnability	N
Country of origin	MX

**Offer Sustainability**

RoHS (date code: YYWW)	Compliant - since 0841 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------