

Product data sheet

Specifications

SQUARE D



Terminal Block Assembly, Pressure Wire Clamp, Natural Color, 600VAC/DC 40AMP

9080GP66

! Discontinued

Main

Range Of Product	9080G
Product Type	Terminal block
Color	Natural

Complementary

Voltage Rating	600 V AC/DC
Current Rating	40 A UL 40 A CSA
Assemblies Consist Of	1 end barrier 2 end clamp(s) 1 mounting track 6 terminal blocks
Wire Size	AWG 18...AWG 12 copper
Mounting Type	9080GH track
Certifications	UL recognized E60616 CCN XCFR2 CE CSA file 62144 class 6228 01
Ambient Air Temperature For Operation	-40...257 °F (-40...125 °C)
Electrical Connrection Tightening Torque	Clamp terminal zinc plated steel 18...20 lbf.in (2.03...2.26 N.m) : AWG 18...AWG 10 copper)
Height	1.48 in (37.59 mm)
Width	1.8 in (45.72 mm)
Depth	5 in (127.00 mm)

Ordering and shipping details

Category	21702-9080 G (NOT GCB)
Discount Schedule	CP5
Gtin	00785901397281
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	8.00 oz (226.796 g)
------------------	---------------------

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)
