

# Product data sheet

Specifications

SQUARE D



## Terminal Block Assembly, Box Lug Connector, Natural Color, 600VAC/DC 60AMP

9080GR64

! Discontinued

### Main

Range Of Product	9080G
Product Type	Terminal block
Color	Natural

### Complementary

Voltage Rating	600 V AC/DC
Current Rating	60 A UL 60 A CSA
Assemblies Consist Of	1 end barrier 2 end clamp(s) 1 mounting track 4 terminal blocks
Wire Size	AWG 22...AWG 8 copper
Mounting Type	9080GH track
Certifications	UL recognized E60616 CCN XCFR2 CE CSA file 62144 class 6228 01
Protection Type	Fingersafe DIN 57470
Ambient Air Temperature For Operation	-40...257 °F (-40...125 °C)
Electrical Connrection Tightening Torque	Lug copper 18...20 lbf.in (2.03...2.26 N.m) : AWG 22...AWG 8 copper)
Height	1.82 in (46.23 mm)
Width	1.72 in (43.69 mm)
Depth	4 in (101.60 mm)

### Ordering and shipping details

Category	21702-9080 G (NOT GCB)
Discount Schedule	CP5
Returnability	No
Country Of Origin	MX

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	16.00 oz (453.592 g)
------------------	----------------------

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

### Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

---