

9080GR66BC

Terminal Block Assembly, Box Lug Connector,
Natural Color, 600VAC/DC 60AMP



Price* : 24.30 USD



9080GR66BC has not been replaced. Please contact your customer care center for more information.

Main

Range of product	9080G
Product or component type	Terminal block
Color	Natural

Complementary


System Voltage	600 V AC/DC
Current Rating	60 A per: UL 60 A per: CSA
Assemblies Consist of	End barrier qty: 1 End clamp(s) qty: 2 Mounting track qty: 1 Terminal blocks qty: 6
Wire Size	AWG 22...AWG 8 (copper)
Mounting Type	9080GH track
Certifications	CE UL recognized E60616 CCN XCFR2 CSA file 62144 class 6228 01
Protection Type	Fingersafe per: DIN 57470
Ambient air temperature for operation	-40...257 °F
Electrical Connrection Tightening Torque	Lug copper Tightening Torque: 18...20 lbf.in for: AWG 22...AWG 8 (copper)
Height	1.82 in
Width	1.72 in
Depth	4 in

Ordering and shipping details

Category	21702 - 9080 G (NOT GCB)
Discount Schedule	CP5
Nbr. of units in pkg.	1

Package weight(Lbs)	2.5
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0935 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------