

# Product data sheet

## Characteristics

# 9080GR67MPO

Terminal Block Assembly, Box Lug Connector,  
Natural Color, 600VAC/DC 60AMP

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 31.10 USD



### Main

Range of product	9080G
Product or component type	Terminal block
Color	Natural

### Complementary

System Voltage	600 V AC/DC
Current Rating	60 A per: UL 60 A per: CSA
Assemblies Consist of	End barrier qty: 1 End clamp(s) qty: 2 Mounting track qty: 1 Marker qty: 1 Terminal blocks qty: 7
Wire Size	AWG 22...AWG 8 (copper)
Mounting Type	9080GH track
Certifications	CE UL recognized E60616 CCN XCFR2 CSA file 62144 class 6228 01
Protection Type	Fingersafe per: DIN 57470
Ambient air temperature for operation	-40...257 °F
Electrical Connrection Tightening Torque	Lug copper Tightening Torque: 18...20 lbf.in for: AWG 22...AWG 8 (copper)
Height	1.82 in
Width	1.72 in
Depth	5 in

### Ordering and shipping details

Category	21702 - 9080 G (NOT GCB)
----------	--------------------------

Discount Schedule	CP5
Nbr. of units in pkg.	1
Package weight(Lbs)	0.76000000000000001
Returnability	N
Country of origin	MX

**Offer Sustainability**

RoHS (date code: YYWW)	Compliant - since 0846 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------