

# Product data sheet

Specifications

SQUARE D



## NEMA Control Relay, replacement relay coil, 12 VDC

9998XD28

 Discontinued on: Oct 11, 2019

 Discontinued

### Main

Range Of Product	8501X
Relay Type	Control relay
Product Or Component Type	Coil

### Complementary

[Uc] Control Circuit Voltage	12 V DC
Coil Voltage Limits	Operational 0.8...1.1 Uc DC
Inrush Power In Watts	18 W
Sealed Power In Watts	18 W
Electrical Connection	Screw clamp terminals
Wire Gauge	AWG 18...AWG 12 copper
Terminal Tightening Torque	Control circuit 9.03...12.04 lbf.in (1.02...1.36 N.m) screw terminals
Height	2 in (50.80 mm)
Width	2.22 in (56.39 mm)
Depth	3 in (76.20 mm)

### Ordering and shipping details

Category	21756-9998 DISCOUNT CP10
Discount Schedule	CP10
Gtin	00785901743361
Returnability	No
Country Of Origin	MX

### Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications