


Product data sheet

Specifications



Acti9 - comb busbar - 3L+N balanced with Aux and Vigi - 9 mm pitch - 56 modules

A9N21038

 **Discontinued on:** Apr 18, 2022

 **Discontinued**

Main

Range	Acti9
Product Or Component Type	Comb busbar
Mounting Mode	Horizontal
Accessory / Separate Part Category	Connection accessory
Lines Description	3L + N
Length In 18 Mm Modules	56

Complementary

Number Of Ways	22 ways Aux + N + L + Vigi
Poles Configuration For 1 Way	1 x 1P + N
Connection Pitch	0.35 in (9 mm) between phase and neutral
Connector Type	tooth
Distance Between Way	1.77 in (45 mm)
Marking	N L1 N L2 N L3
Insulation	Insulated
Device Presentation	Cuttable
[Ie] Rated Operational Current	63 A 104 °F (40 °C)
[Ue] Rated Operational Voltage	230 V AC Ph/N
[Ui] Rated Insulation Voltage	500 V AC IEC 61439-2
Mounting Location	Top tunnel type terminals
9 Mm Pitches	112
Width	39.37 in (1000 mm)
Color	Light gray RAL 7035)
Range Compatibility	Acti 9 Acti9 C40 Acti 9 Acti9 DT40 Acti 9 Acti9 DT40 Vigi Acti 9 Acti9 iDPN Acti 9 Acti9 DT60 Acti 9 Acti9 DPN Vigi Multi9 Multi9 N40 Vigi

Environment

Standards	IEC 60947-7-1 IEC 61439-2
-----------	------------------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Fire Resistance	1760 °F (960 °C) 30 s) IEC 60695-2-1
Pollution Degree	3 IEC 60947-7-1
Ip Degree Of Protection	IP20 with end-pieces and tooth covers

Ordering and shipping details

Gtin	3606480504761
------	---------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.18 in (3.000 cm)
Package 1 Width	1.97 in (5.000 cm)
Package 1 Length	38.19 in (97.000 cm)
Package 1 Weight	27.23 oz (772.000 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	3.35 in (8.500 cm)
Package 2 Width	42.13 in (107.000 cm)
Package 2 Length	3.94 in (10.000 cm)
Package 2 Weight	9.20 lb(US) (4.175 kg)
Unit Type Of Package 3	P12
Number Of Units In Package 3	200
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	31.50 in (80.000 cm)
Package 3 Length	47.24 in (120.000 cm)
Package 3 Weight	394.63 lb(US) (179.000 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.